

# Encore® HD

Manual powder coating system



## Achieve savings on your powder line with precision process control.

The Encore HD Manual Powder Spray System is our fourth generation high density, low velocity (HDLV) spray technology. Designed for superior process control, you can achieve a highly dense phase spray, a more diluted mixture... or anything in between. HDLV technology delivers a high concentration of powder, but using very little air. As a result, you get greater transfer efficiency, less overspray and superior cured finish quality for every conceivable part type. The latest system is configured in many ways to meet everyday application demands.

- **Mobile.**  
Hopper and VBF
- **Standalone.**  
Single and dual
- **Wall Mount**
- **Rail Mount**

### The application



### The spray gun

- Lightweight, well-balanced spray gun to make the painter's job easier.
- Powder deposition at speeds nearly double that of venturi systems
- Superior edge and corner coverage with one pass
- Higher transfer efficiency
- On-gun controls for fast, easy adjustments
- Uniform spray patterns with all powders, even the most challenging materials
- Highly durable lance extensions for fast color-change environments
- 100kV multiplier delivering maximum first pass transfer efficiency



**5/2**  
**Warranty**  
5-YEAR WARRANTY ON NON-WEAR PARTS.  
2-YEAR WARRANTY ON CABLES.

**Nordson**

## The nozzles

- Common Encore nozzle family lowers cost of ownership



- Designed to resist wear and impact fusion
- Variety of nozzle offerings accommodates numerous applications
  - Large surfaces
  - Intricate parts
  - Deep recesses
  - Bottom and top surfaces

## The controller

- Closed loop digital flow control for consistent, repeatable output
- Patented AFC control for the highest finish quality
- NFC allows small incremental adjustments under 10 microamps and independent kV control to achieve a smooth finish, even using the most challenging powder materials
- 20 available preset modes to make operation easier
- Customized control programs to adjust to any application need



## The pump


- Built to deliver up to 750 grams per minute
- Developed to perform 10 million cycles without maintenance
- Repeatable performance after continuous duty
- Patented clear housing provides visibility to valves during operation
- Distributes more powder, using less air
- Designed for automated color changing



## The system

Introducing the first commercially available HDLV mobile system designed to feed from a box. HDLV is now easily mobile and configured to accommodate box fed and 50 lb hopper fed applications. Each system is specialized with a unique pick up tube engineered for superior fluidization and easy cleaning.

The new Encore HD manual system configurations also include standalone and wall/rail mount systems to complement several types of applications.



### Technical specifications

#### Encore HD manual gun

<b>Height</b>	25.4 cm (10.00 in.)
<b>Length</b>	3.8 cm (13.30 in.)
<b>Weight</b>	530 gm (18.70 oz.)
<b>Pump</b>	
<b>Output (Max)</b>	750 g/min (1.65 lbs/min)
<b>Minimum operating air pressure</b>	5.8 bar (85 psi)
<b>Total air consumption</b>	85 l/min (3 cfm)
<b>Color change air consumption</b>	283 l/min (10 cfm)

© 2018 Nordson Corporation | All Rights Reserved | PWL-18-5823 | Revised 3/18

### Nordson Industrial Coating Systems

100 Nordson Drive  
Amherst, OH, 44001  
USA

Phone: +1.440.985.4000  
[www.nordson.com/ics](http://www.nordson.com/ics)

 /Nordson\_Coating

 /NordsonICS

 /company/nordson-industrial-coating-systems

Find your local Nordson office:  
[www.nordson.com/icslocations](http://www.nordson.com/icslocations)

Performance by design

